

MOTIP Effect Metallic

Ord.-no.: look at ordering information

Technical Information



Fast-drying lacquer to treat surfaces of wood, metal, aluminium, glass, stone and various types of plastic. Metallic Lacquer is rub resistant, scratch free and wear-resistant and resistant to weather influences. MoTip Deco Effect Metallic Lacquer is available in 13 colours.

Quality & properties

- Fast drying
- Rub resistant
- Non-fading and UV resistant
- Scratch free and shock proof
- Resistant to weather influences
- Scratch free and wear-resistant
- Excellent adhesion

Physical & chemical data

- Base: Nitrocombi resin
- Colourname:
 - ◊ Brilliant Silver
 - ◊ Aluminium
 - ◊ Sparkling Silver
 - ◊ Silver
 - ◊ Gold
 - ◊ Brilliant Gold
 - ◊ Real Gold
 - ◊ Antique Gold
 - ◊ Blue
 - ◊ Black
 - ◊ Red
 - ◊ Violet
 - ◊ Green
- Efficiency: – 1,25 - 1,75 m²
- Dry to touch: 10 - 20 min
- Dust dry: 5 - 10 min
- Completely dry: 120 min
- Overcoatable: 120 min
- Surfaces:
 - ◊ wood, metal, aluminium, glass, stone and various types of plastic
 - ◊ wood, metal, aluminium, glass, stone and various types of plastic
- Minimum Working Temperature: 15 °C
- Maximum Working Temperature: 25 °C
- Vapour pressure:
 - ◊ 4000/20 bar
 - ◊ 3500/20 bar
- Flash point: n.a. °C
- Temperature Resistance: – 110 °C
- Content: 12 ML

How to use

- The surface should be clean, dry and free of grease. Slightly sand the surface (grain 600).
- The surface should be clean, dry and free of grease. The aerosol should have room temperature. Best processing temperature 10 to 25°C. Before use, shake the aerosol for 2 minutes and spray a sample. Distance to the surface to be treated approximately 25 to 30 centimetre.
- Apply the lacquer in several thin layers. Before applying the next layer, again shake the aerosol.
- After use, clean the valve (turn aerosol upside down and press the nozzle for approximately 5 seconds).
- The drying time depends on the ambient temperature, the humidity of the air and the thickness of the lacquer applied.

Environmentally sound

European Aerosols is committed to apply formulations without restricted or critical ingredients and to achieve best possible performance. The caps and packagings are made of recyclable material.

Disposal

Only the completely emptied cans should be put into the recycling skip or appropriate container for reclaimable refuse. Cans which are not empty should be disposed off as "special refuse".

Marking/Labeling

All products made by European Aerosols comply with the actual labelling regulations according to Preparation Guideline 1999/45/EG. All aerosols correspond to TRGS 200 and TRG 300 as well as to aerosol guideline 75/324/EWG in the actually valid version.

For any further technical questions call our hotline +31 (0) 561 69 44 55 from Monday to Thursday from 9 h a.m. to 3 h p.m. or on Friday until 12 h p.m.

As of November 24, 2021 – This release replaces all eventually earlier issued versions.

European Aerosols GmbH, Kurt-Vogelsang-Straße 6, 74855 Haßmersheim - [info-de\(at\)european-aerosols.com](mailto:info-de(at)european-aerosols.com)
European Aerosols B.V., Wolframweg 2, NL-8471 XC Wolvega - [info-nl\(at\)european-aerosols.com](mailto:info-nl(at)european-aerosols.com)