

## MOTIP Carat Styropor Primer

Ord.-no.: 08107

### Technical Information



Fast drying, insulating primer for surfaces of styropor. Carat Styropor Primer is Re-sprayable with all lacquer systems.

#### Quality & properties

- Fast drying
- Excellent insulating properties
- Re-sprayable with all lacquer systems

#### Physical & chemical data

- Base: Acrylic resin
- Colourname: White
- Degree of gloss: mat, 10 ±2 GU
- Completely dry: 3 uur min
- Overcoatable: 3 uur min
- Surfaces: High quality, insulating primer for surfaces of styropor.
- Minimum Working Temperature: 15 °C
- Maximum Working Temperature: 25 °C
- Vapour pressure: 3500/20 bar
- Flash point: n.a. °C
- Content: 400 ML

#### How to use

- The surface should be clean, dry and free of grease. Remove loose old lacquer and rust and sand the surface.
- The surface should be clean, dry and free of grease. The aerosol should have room temperature. Best processing temperature 15 to 25°C. Before use, shake the aerosol for 2 minutes and spray a sample. Distance to the surface to be treated approximately 25 to 30 centimetre.
- Apply the primer in several thin layers. Before applying the next layer, again shake the aerosol.
- After use, clean the valve (turn aerosol upside down and press the nozzle for approximately 5 seconds).
- After use, clean the valve (turn aerosol upside down and press the nozzle for approximately 5 seconds).

#### Environmentally sound

European Aerosols is committed to apply formulations without restricted or critical ingredients and to achieve best possible performance. The caps and packagings are made of recyclable material.

#### Disposal

Only the completely emptied cans should be put into the recycling skip or appropriate container for reclaimable refuse. Cans which are not empty should be disposed off as "special refuse".

#### Marking/Labeling

All products made by European Aerosols comply with the actual labelling regulations according to Preparation Guideline 1999/45/EG. All aerosols correspond to TRGS 200 and TRG 300 as well as to aerosol guideline 75/324/EWG in the actually valid version.

For any further technical questions call our hotline +31 (0) 561 69 44 55 from Monday to Thursday from 9 h a.m. to 3 h p.m. or on Friday until 12 h p.m.

As of November 24, 2021 – This release replaces all eventually earlier issued versions.