

## MOTIP Carat Gold and Carat Silver

Ord.-no.: 08037, 08036

### Technical Information



MoTip Carat is a high quality decorative acrylic lacquer, with the properties of a car refinishing lacquer. However, with the advantage that the application is so user friendly that now everyone can benefit from the advantages of a spray can. The Carat assortment consists of primers, plastic primer, several trendy lacquers, some effect lacquers (chrome and sparkle) and a special primer for styropor.

### Quality & properties

- Excellent coverage
- Lasting colour and gloss
- Scratch free and wear-resistant
- Excellent vertical stability so hardly any dripping
- Resistant to chemicals and weather influences
- Excellent adhesion

### Physical & chemical data

- Base: Acrylic resin
- Colourname:
  - ◊ Gold
  - ◊ Silver
- Degree of gloss: high gloss, >85 GU
- Efficiency: 400 ML – 1,25 - 1,75 m<sup>2</sup>
- Dry to touch: 10 min
- Dust dry: 5 min
- Completely dry: 60 min
- Overcoatable: 60 min
- Surfaces: wood, metal, aluminium, glass, stone and various types of plastic.
- Minimum Working Temperature: 15 °C
- Maximum Working Temperature: 25 °C
- Vapour pressure: 4000/20 bar
- Flash point: n.a.
- Temperature Resistance: – 110 °C
- Content: 400 ML

### How to use

- The surface should be clean, dry and free of grease. Remove loose old lacquer and rust, sand the surface and apply a layer of Carat primer. When treating surfaces of plastic, first apply a layer of Carat plastic primer before applying the Carat primer. After drying, sand the base layer (grain 600).
- The surface should be clean, dry and free of grease. The aerosol should have room temperature. Best processing temperature 15 to 25°C. Before use, shake the aerosol for 2 minutes and spray a sample. Distance to the surface to be treated approximately 25 to 30 centimetre.
- Apply the lacquer in several thin layers. Before applying the next layer, again shake the aerosol.
- After use, clean the valve (turn aerosol upside down and press the nozzle for approximately 5 seconds).
- After use, clean the valve (turn aerosol upside down and press the nozzle for approximately 5 seconds).

### Environmentally sound

European Aerosols is committed to apply formulations without restricted or critical ingredients and to achieve best possible performance. The caps and packagings are made of recyclable material.

### Disposal

Only the completely emptied cans should be put into the recycling skip or appropriate container for reclaimable refuse. Cans which are not empty should be disposed off as "special refuse".

### Marking/Labelling

All products made by European Aerosols comply with the actual labelling regulations according to Preparation Guideline 1999/45/EG. All aerosols correspond to TRGS 200 and TRG 300 as well as to aerosol guideline 75/324/EWG in the actually valid version.

For any further technical questions call our hotline +31 (0) 561 69 44 55 from Monday to Thursday from 9 h a.m. to 3 h p.m. or on Friday until 12 h p.m.

European Aerosols GmbH, Kurt-Vogelsang-Straße 6, 74855 Haßmersheim - [info-de\(at\)european-aerosols.com](mailto:info-de(at)european-aerosols.com)  
European Aerosols B.V., Wolfraamweg 2, NL-8471 XC Wolvega - [info-nl\(at\)european-aerosols.com](mailto:info-nl(at)european-aerosols.com)