

MOTIP Motip Hybrid Clear Lacquer

Ord.-no.: 304601, 304602, 304603

Technical Information



HYBRID spray paint produces beautiful, high-gloss results. The lacquer can be applied without primer to many bases, even to polystyrene. HYBRID spray paint can easily and without any problems be applied over existing paint layers without running. Low odour HYBRID spray paint is strong and dries quickly, making it scratch-resistant. An ideal spray to help you express your creative ideas right away. Unleash your creativity!

Quality & properties

- Based on a revolutionary resin technology
- Extremely flexible
- UV-resistant and weather resistant
- Scratch resistant
- For indoor and outdoor

Physical & chemical data

- Base: Water based polyurethane resin
- Colourname: Transparent
- Degree of gloss:
 - ◊ semi gloss, 45 ±5 GU
 - ◊ gloss, >75 GU
 - ◊ mat, 10 ±2 GU
- Efficiency: 400 ML – 1 - 1.5 m²
- Dry to touch: 45 min
- Dust dry: 10 - 20 min
- Completely dry: 24 h
- Overcoatable: 2 h
- Surfaces: metal, stone, wood, plastic, glass and textile fabric bases
- Minimum Working Temperature: 10 °C
- Maximum Working Temperature: 25 °C
- Vapour pressure: 4000/20 bar
- Flash point: n.a. °C
- Temperature Resistance: – 10-25 °C
- Content: 400 ML

How to use

- The surface should be clean, dry and free of grease. Remove loose old lacquer and rust and sand the surface.
- The surface should be clean, dry and free of grease. The aerosol should have room temperature. Best processing temperature 15 to 25°C. Before use, shake the aerosol for 2 minutes and spray a sample. Distance to the surface to be treated approximately 25 to 30 centimetre.
- Apply the lacquer in several thin layers. Before applying the next layer, again shake the aerosol.
- After use, clean the valve (turn aerosol upside down and press the nozzle for approximately 5 seconds).
- The drying time depends on the ambient temperature, the humidity of the air and the thickness of the lacquer applied.

Environmentally sound

European Aerosols is committed to apply formulations without restricted or critical ingredients and to achieve best possible performance. The caps and packagings are made of recyclable material.

Disposal

Only the completely emptied cans should be put into the recycling skip or appropriate container for reclaimable refuse. Cans which are not empty should be disposed off as "special refuse".

Marking/Labelling

All products made by European Aerosols comply with the actual labelling regulations according to Preparation Guideline 1999/45/EG. All aerosols correspond to TRGS 200 and TRG 300 as well as to aerosol guideline 75/324/EWG in the actually valid version.

For any further technical questions call our hotline from Monday to Thursday from 9 h a.m. to 3 h p.m. or on Friday until 12 h p.m.

European Aerosols GmbH, Kurt-Vogelsang-Straße 6, 74855 Haßmersheim - [info-de\(at\)european-aerosols.com](mailto:info-de(at)european-aerosols.com)
European Aerosols B.V., Wolfraamweg 2, NL-8471 XC Wolvega - [info-nl\(at\)european-aerosols.com](mailto:info-nl(at)european-aerosols.com)